

SBK-Installation kit for one pipe manifold 2000 / 3000

Because of on site conditions it isn't always possible to install the supply and return manifold beams separately. Therefore we have the installation kits for one pipe manifold 3000 and 2000 in our product range. The manifold beams can be assembled in one line with these installation kits. The series 3000 has an overall height of 80 mm, the series 2000 of 75 mm.

Each installation kit consists of:

Connection block diagonally drilled with o-ring	1 pcs
Separation plate 5 mm black with o-ring	1 pcs
Intermediate plate 2 mm black	1 pcs
Sleeve nut M8x25 galvanized	2 pcs

Additionally the wall or cabinet holder 75 mm high (Item no. 6.013.029) is required.

The installation kits differ only in the type of their connection blocks diagonally drilled 3000 or 2000.

Installation information:

- Screw in threaded bars M8 into standard connection block.
- Put off one required supply module after the other.
- Put off separation plate 5 mm black with o-ring (pay attention to position of o-ring).
- Put off the required number of return modules.
- Put off intermediate plate 2 mm black.
- Put off connection block diagonally drilled and screw it with sleeve nuts M8x25 galvanized.

